

---

## Phase Selector

**chiralpak ic - an immobilized polysaccharide chiral ...** - chiralpak® ic tm - an immobilized polysaccharide chiral stationary phase with a unique chiral selector clint chiral technologies, incamos, geoff cox, , west chester, pa **low high - accuphase** - 547w 131w 232w 370w 60w 8 4 2 1 max. output power 50 100 150 200 250 300 350 400 450 500 550 impedance (ohms) rated output power 480w 240w 120w - input + input output **variable transformers product selector guide - variac** - product quick selector see legend on last page. the staco variable transformer product quick selector is a guide to all standard single-phase and three-phase vari- **pow-r-stock plus quick selector reference guide** - pow-r-stockplus quick selector reference guide frequently used distribution and control products available from distributor stock **power modules - vishay** - standard diode and thyristor modules versatile and high-efficiency power diode and scr modules from vishay intertechnology feature industry-standard **m separate mm/mc ampli m - accuphase** - m separate mm/mc amplifier circuitry ensures ultra low noise m highly precise equalization with only  $\pm 0.3$  db riaa deviation m versatile impedance switching with **phase-adaptive power module - lutron electronics** - ee e e 369356e 1 09.14.17 lutron e e ® specification submittal page e e e e phase-adaptive power module description • ovides capability for a zone on a grafik pr eye control **lut-eli-3ph emergency lighting interface - lutron electronics** - line voltage wiring examples: 3-phase diagram split phase diagram 'facp' n/c contacts 'facp' n/o 121110987654321 class 2 low voltage wiring gnd sense drain mux +24vfw common not used **e cient conversion of hplc instruments between normal ...** - 6 liquid chromatography sigma-aldrich/hplc order: 800-247-6628 (us only) / 814-359-3441 reporter 28.5 e!cient conversion of hplc instruments between **bsv-p centralized branch selector units - daikin ac** - specifications edus391100-f13 2 bsv-p 1. specifications centralized branch selector units notes: 1 in case of connecting with a 07~18 type indoor unit, match to the size of field pipe using the attached pipe. **individual branch selector for vrv iv heat recovery - bs1q-a** - bs1q10a bs1q16a bs1q25a power input cooling nom. kw 0.005 heating nom. kw 0.005 maximum number of connectable indoor units 6 8 maximum capacity index of connectable indoor units  $15 < x \leq 100$  100